



Level of firmness:

Medium soft

NO FLIP

Side 1



ANTI-MITE
MATTRESS



HYPOALLERGENIC
FABRIC



TOUCH
FOAM



TITANIUM
SPRINGS



WASHABLE
AT 60°

Mattress height: 35 CM.

REMOVABLE COVER.

N.B.: Covers with widths up to 120 cm will fit into a household washing machine.

Titanium springs with differentiated areas and topper in touch foam that moulds perfectly to the contours of the body.

1_ OUTER COVER

Made of hypoallergenic fabric with high breathability and exclusive zinc treatment, soft to the touch and gentle on the skin. Subjected to a permanent hypoallergenic procedure resistant to repeated washings. The cover can be divided into two parts with perimeter zip, and is machine washable at 60° C.

2_ SPRINGS

Consisting of 400/800 exclusive independent pocketed titanium springs, combined with a special perimeter profile in tempered steel that runs along the mattress for calibrated and long-lasting support. The use of titanium allows increasing the resistance to stress over time and maintaining the performance for longer. This makes the mattress easier to handle and 40% lighter than traditional steel springs.

3_ TOP MASSAGING LAYER

Made of high density (DN60) "eco-friendly polyurethane foam" hydrophilic and resilient for strong support. It ensures perfect extension of the back when resting.

4_ SIDE BOX

Encloses the springs. It is made of polyurethane foam with maximum density of DN 70 to guarantee perfect balancing of the resting surface. It makes the mattress robust and load-bearing.

5_ PADDING IN SILK AND WOOL (TWO OVERLAPPING LAYERS)

Silk: high quality, absorbs excess humidity. Virgin wool: durable and elastic, it disperses excess moisture making the resting surface fresh and dry.


6_ SIDE 1 REMOVABLE TOPPER

It enhances the elasticity of the support. The cover is machine washable at 60°. The core in touch foam is very elastic, breathable and hydrophilic. It compresses and returns to fullness: does not compact. It disperses humidity, and stays cool and dry.

7_ NO FLIP MATTRESS: IT IS ONLY USED ON ONE SIDE

It is recommended to regularly rotate the mattress from head to foot.

FITTED WITH HANDLES



PRODUCT CODE 1/P: **62051**

PRODUCT CODE 2/P: **62057**